


DECLARATION OF COMPATIBILITY

between Ecolab hygiene products and
Telemecanique Food and Beverage processing series sensors.

For the completely safe cleaning of your detection equipment



**Sensors designed for
Food and Beverage processing
industries:**

**Type2 and Type4 Safety Light Curtains
with IP69K sealed protection tube**



The declaration concerns tests relating to sealing and electrical operation, both before and after the use of the ECOLAB cleaning products stated, and therefore proves the high resistance of these sensors to detergent products.



**Supplier of hygiene solutions for
Food and Beverage industries**


Products



Equipments



Services



Compatible products

Chemicals and chemical families	XUSL4E●●●●●NWC XUSL2E●●●●●NWC XUSL4E●●●●●NWH XUSL2E●●●●●NWH
P3-topax 52 (5%) Acid foaming detergent	●
P3-topactive 200 DK (5%) TFC alkaline detergent	●
P3-topax 66 (3%) Chlorinated alkaline foaming biocide	●
P3-topactive OKTO (3%) Oxidizing biocide without chlorine	●
P3-topax 990 (3%) Neutral non-oxidizing biocide	●

Beware of limited compatibility of the protection tube with P3-alcodes or any alcohol-based cleaning agent

Test procedure

Ecolab reference method – Test performed by Telemecanique Sensors

- Full immersion of parts in detergent solutions
- water hardness of 300ppm CaCO₃
- 28 days total time at 20°C
- Concentrations tested higher than those recommended
- Visual evaluation followed by tests to verify correct operation
- Telemecanique Sensors test reports: R-Dev-13-0491

For optimal application of Ecolab products please refer to Ecolab specific open surfaces hygiene recommendations

